OFFICE USE ONLY APPLICATION FOR OSHPD SPECIAL SEISMIC **CERTIFICATION PREAPPROVAL (OSP) APPLICATION #:** OSP - 0173-10 **OSHPD Special Seismic Certification Preapproval (OSP) Manufacturer Information** JOHNSON THERMAL SYSTEMS Manufacturer: Manufacturer's Technical Representative: Jeff Johnson Mailing Address: 1614 Industrial Way, Ste.104, Caldwell, ID. 83605-6925 Telephone: On File Email: On File **Product Information** Product Name: JTS CHILLERS Product Type: Air-Cooled Process Chillers Product Model Number: **SEE ATTACHMENT 1** (List all unique product identification numbers and/or part numbers) General Description: Chillers for medical equipment cooling, data center cooling, space cooling and dehumidification. Chiller frame is constructed from G90 galvanized steel members. All cover panels are powder coated carbon steel. Cabinets have NEMA 4 electrical enclosure. Structural enhancements incorporated in the test units and required to anomalies observed during test shall be incorporated into all certified units. Mounting Description: Rigid Base mounted. **Applicant Information** Applicant Company Name: EASE Co. Contact Person: Jonathan Roberson, S.E. Mailing Address: 5877 Pine Ave, Suite 210, Chino Hills, CA. 91709 Telephone: (909) 606-7622 Email: j.roberson@easeco.com I hereby agree to reimburse the Office of Statewide Health Planning and Development review fees in accordance with the California Administrative Code, 2016. Signature of Applicant: Date: 2/20/2017 Title: Principal Structural Engineer Company Name: EASE Co.

"Access to Safe, Quality Healthcare Environments that Meet California's Diverse and Dynamic Needs'





02/21/2017 OSP-0173-10 Page 1 of 7



OFFICE OF STATEWIDE HEALTH PLANNING AND DEVELOPMENT FACILITIES DEVELOPMENT DIVISION

STATE OF CALIFORNIA – HEALTH AND HUMAN SERVICES AGENCY OSH-FD-759 (REV 12/16/15)

Page 2 of 3





OFFICE OF STATEWIDE HEALTH PLANNING AND DEVELOPMENT FACILITIES DEVELOPMENT DIVISION

STATE OF CALIFORNIA – HEALTH AND HUMAN SERVICES AGENCY OSH-FD-759 (REV 12/16/15)

Page 2 of 3

Seismic Parameters
Design in accordance with ASCE 7-10 Chapter 13: ⊠ Yes ☐ No
Design Basis of Equipment or Components (Fp/Wp) = 2.16 (30 Ton Chiller) 1.99 (All other model in Table 1)
S _{DS} (Design spectral response acceleration at short period, g) = 3.0 (30 Ton Chiller) 2.77 (All others)
a _p (In-structure equipment or component amplification factor) = 1
R _p (Equipment or component response modification factor) = 2½
Ω_0 (System overstrength factor) = 2
I _p (Importance factor) = 1.5
z/h (Height factor ratio) = 1
Equipment or Component Natural Frequencies (Hz) = See Attachment 2
Overall dimensions and weight (or range thereof) = See Attachment 1
Equipment or Components @ grade designed in accordance with ASCE 7-10 Chapter 15: Yes No
Design Basis of Equipment or Components (V/W) =
S _{DS} (Design spectral response acceleration at short period, g) =
S _{D1} (Design spectral response acceleration at 1 second period, g) =
R (Response modification coefficient) =
Ω_0 (System overstrength factor) =
C _d (Deflection amplification factor) =
I_p (Importance factor) = 1.5
Height to Center of Gravity above base =
Equipment or Component Natural Frequencies (Hz) =
Overall dimensions and weight (or range thereof) =
Tank(s) designed in accordance with ASME BPVC, 2015: ☐ Yes ☒ No
List of Attachments Supporting Special Seismic Certification
Other(s) (Please Specify): Attachments 1 & 2
OSHPD Approval (For Office Use Only) – Approval Expires on December 31, 2022
Signature: Date: 2/21/2017
Print Name: M. R. Karim Title: SHFR Special Seismic Certification Valid Up to: S _{DS} (g) = See Above z/h = 1.0
Condition of Approval (if applicable):
Condition of Approval (ii applicable).

"Access to Safe, Quality Healthcare Environments that Meet California's Diverse and Dynamic Needs"

02/21/2017



OSHPD



ATTACHMENT 1: SEISMIC CERTIFIED COMPONENTS

ATTACHMENT PAGE | 1 OF 3

TABLE 1: SEISMIC CERTIFIED SYSTEMS & COMPONENTS

JOHNSON THERMAL	. SYSTEMS						
CHILLERS							
		D	MENSIONS	(IN.)	MAX. WT.		
OMPONENT	PART NO.	W	D	H	(LB.)	MOUNTING	BASIS [1]
r (SAC)	JTS3SAC-OSP	34	60	60	690	Rigid Base	INT
r (SAC)	JTS4SAC-OSP	34	60	60	690	Rigid Base	INT
r (SAC)	JTS5SAC-OSP	34	60	60	700	Rigid Base	UUT1
r (SAC)	JTS7SAC-OSP	42	83	78	1050	Rigid Base	INT
r (SAC-HA)	JTS7SAC-HA-OSP	42	83	78	1200	Rigid Base	INT
er (SAC)	JTS10SAC-OSP	42	83	78	1100	Rigid Base	INT
er (SAC-HA)	JTS10SAC-HA-OSP	42	83	78	1164	Rigid Base	INT
er (DIAC)	JTS10DIAC-OSP	52	79	80	1750	Rigid Base	INT
er (DIAC)	JTS15DIAC-OSP	52	79	80	1800	Rigid Base	INT
er (DIAC-HA)	JTS15DIAC-HA-OSP	52	79	80	1950	Rigid Base	INT
er (DIAC)	JTS20DIAC-OSP	52	79	80	1950	Rigid Base	INT
er (DIAC-HA)	JTS20DIAC-HA-OSP	52	79	80	1950	Rigid Base	INT
er (DIAC)	JTS25DIAC-OSP	68	79	88	2200	Rigid Base	INT
er (DIAC-HA)	JTS25DIAC-HA-OSP	68	79	88	2250	Rigid Base	INT
er (DIAC)	JTS30DIAC-OSP	68	79	88	2250	Rigid Base	UUT2
1. BASIS: • UUT#: Indicates • INT (Interpolate	base. s that a test specimen mad or Extrapolated): indica	itching the	se characterist	ics was teste	ed as part of this tested, and by w	testing program.	
	CHILLERS DMPONENT (SAC) (SAC) (SAC) (SAC) (SAC-HA) (SAC	PART NO. r (SAC) r (SAC) JTS3SAC-OSP r (SAC) JTS4SAC-OSP r (SAC) JTS7SAC-OSP r (SAC) JTS7SAC-OSP r (SAC-OSP r (SAC) JTS10SAC-OSP r (SAC) JTS10SAC-OSP r (DIAC-OSP r (DI	CHILLERS PART NO. (SAC) (SA	DIMENSIONS	DIMENSIONS (IN.) DIMENSIONS	DIMENSIONS (IN.) MAX. WT. (LB.)	DIMENSIONS (IN.) MAX. WT. (LB.) MOUNTING

Phone (909) 606-7622 | OSP@EaseCo.com

02/21/2017 OSP-0173-10 Page 4 of 7



ATTACHMENT 1: SEISMIC CERTIFIED COMPONENTS

ATTACHMENT PAGE | 2 OF 3

TABLE 2: CHILLER SUBASSEMBLIES ACCEPTED IN SEISMIC CERTIFICATION

	MAX. DIMENSIONS (IN) MAX.								
MANUFACTURER	PRODUCT LINE	MODEL	DIAM LENGTH WIDTH HEIGHT			WT. (LB)	NOTES		
COMPRESSORS									
	Digital Scroll Compressor,								
COPELAND	Hermetic R-410a	ZPD34K5E	N/A	9.57"	9.57"	17.66"	68.2 lb		
001 227 1112	Digital Scroll Compressor,	Zi Bo ii to z	1 177 1	0.01	0.01	11.00	00.2 10		
COPELAND	Hermetic R-410a	ZPD51K5E	N/A	9.26"	9.26"	18.39"	72.8 lb		
	Digital Scroll Compressor,			00			1 = 10 10		
COPELAND	Hermetic R-410a	ZPD61KCE	N/A	9.63'	9.82"	17.91"	88.8 lb	UUT1	
	Digital Scroll Compressor,								
COPELAND	Hermetic R-410a	ZPD103KCE	N/A	11.54"	11.23"	21.00"	134 lb		
	Digital Scroll Compressor,								
COPELAND	Hermetic R-410a	ZPD120KCE	N/A	11.54"	11.23"	21.00"	136 lb		
	Digital Scroll Compressor,								
COPELAND	Hermetic R-410a	ZPD83KCE	N/A	9.48"	9.70"	19.46"	89.9 lb		
	Digital Scroll Compressor,								
COPELAND	Hermetic R-410a	ZPD137KCE	N/A	10.38"	11.23"	21.00"	137 lb		
00051 4415	Digital Scroll Compressor,	700454405		40.000	44.04"	04 70"	44411		
COPELAND	Hermetic R-410a	ZPD154KCE	N/A	12.83"	11.61"	21.72"	144 lb		
CODELAND	Digital Scroll Compressor,	7DD400KCE	NI/A	40.00"	44 64"	04 74"	44716	LILITO	
COPELAND	Hermetic R-410a	ZPD182KCE	N/A	12.83"	11.61"	21.71"	147 lb	UUT2	
RESERVOIR	00			I	ı				
ITC	Custom SS water/glycol	45T MOOE 4 D	40"	64 4/0"	18"	20"	70 lb		
JTS	reservoir, closed Custom SS water/glycol	15T-M005-1-B	18"	64 1/2"	10	20"	70 lb		
JTS	reservoir, closed	JTS4SAC-V001	18"	22 1/2"	18"	20"	45 lb		
313	Custom SS water/glycol	J1343AC-V001	10	22 1/2	10	20	45 10		
JTS	reservoir, closed	15T-M005-1-B	18"	64 1/2"	18"	20"	70 lb	UUT1	
010	Custom SS water/glycol	101 W000 1 B	10	0+ 1/2	10	20	7010	0011	
JTS	reservoir, closed	JTS4SAC-V001	18"	22 1/2"	18"	20"	45 lb	UUT2	
PUMP	, , , , , , , , , , , , , , , , , , , ,	0.0.0.0							
	End suction centrifugal								
Goulds	pump, single impeller	1ST1G5A4	9"	14.5"	9"	10"	45 lb	UUT1	
	End suction centrifugal								
Goulds	pump, single impeller	1ST1E5C4	9"	14.5"	9"	10"	45 lb		
	End suction centrifugal								
Goulds	pump, dual impeller	LCC1J2D0	6.75"	21.2"	6.75"	9.37"	57 lb	UUT2	
	End suction centrifugal								
Weber	pump, dual impeller	FC40B50-3T	10"	21"	10"	10"	64 lb	UUT2	
FAN ASSEMBLY									
	FN Series, EC Axial motor								
Ziehl-Abegg	driven, 500 mm	FN050-4DQ.4I.V7P1	N/A	26"	26"	6"	37 lb	UUT2	
	FN Series, EC Axial motor	FN071-							
Ziehl-Abegg	driven, 710 mm	ZIQ.DG.V7P3	N/A	33 1/2"	33 1/2"	9"	49 lb	UUT2	
EDM Date (W3G Series, EC Axial	W3G500-CE33-01	NI/A	00"	00"	0"	07 "	1111574	
EBM-Pabst	motor driven, 500 mm	3/60/460	N/A	26"	26"	6"	37 lb	UUT1	
	W3G Series, EC Axial	W3G650-CK02-03	NI/A	22 4/0"	22 4 /0"	9"	40 15	LILITO	
EBM-Pabst	motor driven, 650 mm	3/60/460	N/A	33 1/2"	33 1/2"	9	49 lb	UUT2	
EVAPORATOR	Drozed Dieto Liest				1				
Alfa Laval	Brazed Plate Heat	AC-30-60EQ-S21	N/A	3.9"	3.7"	12.8"	14.2 lb	UUT1	
Alla LaVal	Exchanger Brazed Plate Heat	MO-30-00EQ-321	IN/A	3.8	3.1	12.0	14.∠ IU	0011	
Alfa Laval	Exchanger	AC-70X-50M	N/A	20 1/2"	4 1/2"	6"	25 lb	UUT2	
	PANSION VALVES	\(\tau\(\tau_\-\)\(\tau\)\(\tau_1\)\(\tau	IN/A	20 1/2	7 1/2	U	2010	0012	
Carel	E2V	E2V24BSM00	N/A	5"	2 1/2"	5/8"	1 1/2"	UUT1	
Carel	E3V	E3V45ASR00	N/A	3"	2 1/2"	1 1/4"	2 lb	UUT2	
Carci	v	LUVTUMUNUU	13//7	J	£ 1/£	1 1/4	∠ IU	0012	

Table continues next page

02/21/2017 OSP-0173-10



ATTACHMENT 1: SEISMIC CERTIFIED COMPONENTS

ATTACHMENT PAGE | 3 OF 3

TABLE 2: CHILLER SUBASSEMBLIES ACCEPTED IN SEISMIC CERTIFICATION

			MAX. DIMENSIONS (IN)			MAX.			
MANUFACTURER	PRODUCT LINE	MODEL	DIAM	DIAM LENGTH		HEIGHT	WT. (LB)	NOTES	
CONDENSER	/								
	Micro-channel	59509901 HTS-D							
Heatcraft	aluminium çoil	Cabinet	N/A	37"	26"	1 1/4"	15 lb	UUT1	
	Micro-channel								
Luvata	aluminium coil	E66005OH	N/A	69"	32 1/2"	1 1/4"	36 lb	UUT2	
FLOW SWITCH									
W.E. Anderson	flow switch	119151	N/A	5"	2"	1"	1 oz	All UUT	
CONTROLLER									
Carel	pCOxs	PCO1000BX0	N/A	5 1/2"	4 1/2"	3"	1 1/2 lb	UUT1	
Carel	pCO3	PCO3000ES0	N/A	9"	4 1/2"	3"	2 lb	UUT2	
PRESSURE RELI	EF VALVE								
Wilkins	pressure relief valve	P-1000A952	N/A	3'	2"	1/4"	6 oz	All UUT	
LIQUID LINE FILT	LIQUID LINE FILTER DRIER								
Flow	liquid line filter drier	30 EK 4155	3 1/2"	3 1/2"	3 1/2"	8"	3 lb	All UUT	
AUTOMATIC AIR	VENT								
McDonnel Mill	automatic air vent	AAV-90	2 1/2"	2 1/2"	2 1/2"	6 1/2"	1 1/2 lb	All UUT	

02/21/2017 OSP-0173-10 Page 6 of 7

JOHNSON THERMAL SYSTEMS ATTACHMENT PAGE | 1 OF 1

ATTACHMENT 2: TEST SPECIMEN SUMMARY

UUT-1 5 TON CHILLER (SAC)

Manufacturer: JOHNSON THERMAL SYSTEMS

Identification: Model No.: JTS5SAC-OSP

Description: Controller: Carel PCOxs

Compressor: (1) Copland Digital Scroll ZPD61KCE 5 Ton

Pump: (1) Goulds 1ST1G5A4 2HP

Fan Assy: (1) EBM-Pabst W3G Series, EC Axial motor driven,

500mm

Evaporator: (1) Alfa Laval Brazed Plate Heat Exchanger

Condensor: (1) Heatcraft HTS-D Cabinet Micro-channel aluminum coil

Refrigerant: R-410a

Cabinet: NEMA 4 electrical enclosure

Tank: 20 gallon

Pressure relief bypass valve, flow switch & liquid line filter drier

Mounting: Rigid Base Mount w/ (4) – 3/8"dia grade 8 bolts.

Unit was full of content during AC156 test

Offic was full of conten	it during AC 150 test								
DIMENSIONS (in.)					LOWEST RESONANT FREQUENCY (Hz.)				
Width	Depth	Height		Weight (lb.)	FRONT-AXIS	SIDE-AXIS	VERT-AXIS	OFF-AXIS	
34	60	60		866	15.2	13.8	8.9	11.1	
Shake Table Test Parameters									
CODE	TEST CRITERIA	S _{DS} (g)	z/h	l _P	A _{FLX-H} (g)	A _{RIG-H} (g)	A _{FLX-V} (g)	A _{RIG-V} (g)	
CBC 2016	ICC-ES AC156	2.77	1	1.5	4.43	3.32	1.86	0.75	

Unit maintained structural integrity and functionality per manufacturer requirements after the ICC-ES AC 156 test

UUT- 2 30 TON CHILLER (DIAC)

Manufacturer: JOHNSON THERMAL SYSTEMS

Identification: Model No.: JTS30DIAC-OSP

Description: Controller: Carel PCOxs

Compressor: (2) Copland Digital Scroll ZPD182KCE 5 Ton

Pump: (1) Goulds 5HP

(1) Weber 5HP

Fan Assy: (2) Ziehl-Abegg,FN Series,EC Axial motor driven,500mm

(1) Ziehl-Abegg,FN Series,EC Axial motor driven,710mm

(1) EBM-Pabst W3GSeries,EC Axial motor driven,650mm

Evaporator: (1) Alfa Laval Brazed Plate Heat Exchanger Condensor: (1) Luvata Micro-channel aluminum coil

Refrigerant: R-410a

Cabinet: NEMA 4 electrical enclosure

Tank: 65 gallon

Pressure relief bypass valve, flow switch & liquid line filter drier

Mounting: Rigid Base Mount w/ (4) – 1/2" dia grade 8 bolts.

Unit was full of content during AC156 test

www.SpecialSeismicCertification.com

DIMENSIONS (in.)						LOWEST RESONANT FREQUENCY (Hz.)				
Width	Depth	Height		Weight (lb.)		FRONT-AXIS	SIDE-AXIS	VERT-AXIS	OFF-AXIS	
68	79	88	2791		8.9	7.7	>50	8.9		
Shake Table Test Parameters										
CODE	TEST CRITERIA	S _{DS} (g)	Z/	/h	I _P	A _{FLX-H} (g)	A _{RIG-H} (g)	A _{FLX-V} (g)	A _{RIG-V} (g)	
CBC 2016	ICC-ES AC156-15	3.0	1	1	1.5	4.80	3.60	2.01	0.81	

Unit maintained structural integrity and functionality per manufacturer requirements after the ICC-ES AC 156 test



Phone (909) 606-7622 | OSP@EaseCo.com

Page 7 of 7

02/21/2017 OSP-0173-10